



Main

Bezel material	Black plastic
Device short name	K
Enclosure type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Mounting diameter	1.18 in (30 mm)

Complementary

Cap/operator or lens colour	black
Contacts type and composition	Without contact block
Operator position information	3 positions
Operator profile	Standard knob
Operator profile	1 projecting push-button
Type of operator	Spring return right to centre

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product certifications	CSA LR24590 class 3211 03 CE UL listed file E42259 CCN NKCR

Ordering and shipping details

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1
GTIN	00785901856641
Nbr. of units in pkg.	1
Package weight(Lbs)	0.13 lb(US) (0.06 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	7.62 in (19.355 cm)
Package 1 width	3.00 in (7.620 cm)
Package 1 Length	19.35 in (49.161 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------