



Main

Product or component type	Motor Circuit Protector
---------------------------	-------------------------

Complementary

Number of Poles	3P
Breaking capacity code	G
Electrical connection	Lugs load Lugs line
Tightening torque	230.12 lbf.in (26 N.m) 0.15...0.29 in ² (95...185 mm ²) (AWG 3/0...350 kcmil)
Height	7.52 in (191.01 mm)
Width	4.12 in (104.65 mm)
Depth	5 in (127.00 mm)

Ordering and shipping details

Category	01107 - H/J ELEC TRIP UNIT MOUNT BREAKER/SW
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	5 lb(US) (2.27 kg)
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------