



## Main

| Range | I-Line |
|-------|--------|
|-------|--------|

## Complementary

|                     |   |
|---------------------|---|
| Main Type           | Main lugs   |
| Width               | 34.38 in (873.25 mm)  |
| Height              | 66 in (1676.40 mm)  |
| Product Destination | Panelboard interior HCP 42 in (1066.80 mm) 86 in (2184.40 mm) |
| Rated Current       | 800 A   |
| Mounting Space      | 99 in (2514.60 mm)  |

## Ordering and shipping details

|                       |                       |
|-----------------------|-----------------------|
| Category              | 00016 - I-LINE PB RTA |
| Discount Schedule     | PE1A                  |
| GTIN                  | 00785901220879        |
| Nbr. of units in pkg. | 1                     |
| Package weight(Lbs)   | 208 lb(US) (94.35 kg) |
| Returnability         | Yes                   |
| Country of origin     | US                    |

## Packing Units

|                  |                   |
|------------------|-------------------|
| Package 1 Height | 1.17 ft (0.356 m) |
| Package 1 width  | 3.25 ft (0.991 m) |
| Package 1 Length | 6.00 ft (1.829 m) |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| PVC free                   | Yes   |

## Contractual warranty

---

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

---