

# PC 609



## PERFORMANCE GRADE, CO-EXTRUDED CLOTH DUCT TAPE

### TYPICAL APPLICATIONS

- For use in the HVAC industry to repair thermal insulation and seal metal ductwork
- Can also be used in the manufactured housing industry to seam bottom boards and for patching, seaming and sealing
- Also used for general purpose packaging, bundling, holding, wrapping and waterproofing, as well as for asbestos and mold remediation

### PRODUCT FEATURES

- Cold temperature adhesion
- Excellent holding power with good conformability
- Easy to unwind and tear
- Made using Polybonded CO-EX Technology®

### CONSTRUCTION

Overall Grade/Function: Performance

Backing: Waterproof polyethylene film with a cloth carrier

Adhesive: Blended rubber

### STANDARD WIDTH(S)

48 mm 72 mm

### STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

### STANDARD CORE SIZE

3 in

### APPLICABLE STANDARDS

Tested in accordance with UL 723

### COLOR(S)



**BLACK**  
(BLK)



**RED**  
(RED)



**SILVER**  
(SIL)



**SILVER PRINTED**  
(SPT)

### PHYSICAL PROPERTIES STANDARD METRIC

Tensile Strength	26 lbs/in width	45.5 N/10 mm
Adhesion to Stainless Steel	64 oz/in width	7.00 N/10 mm
Thickness	10 mils	0.25 mm
Elongation	16%	16%
Service Temperature Range	25 F to 200 F	-4 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PTSC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent product specifications or a guarantee of product performance. Individual rolls may vary from these standards (or physical properties). The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

### STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

