



Main

| | |
|------------------------------|---------------------------------------|
| Range | TeSys |
| Product or component type | Contactor coil |
| Device short name | LXD1 |
| Control circuit type | AC at 50/60 Hz |
| [Uc] control circuit voltage | 220 V AC 50/60 Hz |
| Average resistance | 515.4 Ohm 68 °F (20 °C) |
| Inductance of closed circuit | 18 H |
| Product compatibility | CAD LC1D09...D38 LC1DT20...DT40 |
| Mechanical durability | 9 Mcycles |
| Maximum operating rate | 3600 cyc/h 140 °F (60 °C) |

Complementary

| | |
|---------------------------------|--|
| Coil technology | Without built-in suppressor module |
| Control circuit voltage limits | Drop-out 0.3...0.6 Uc 50/60 Hz 140 °F (60 °C) Operational 0.8...1.1 Uc 50 Hz 140 °F (60 °C) Operational 0.85...1.1 Uc 60 Hz 140 °F (60 °C) |
| Inrush power in VA | 70 VA 60 Hz 0.75 68 °F (20 °C) 70 VA 50 Hz 0.75 68 °F (20 °C) |
| Hold-in power consumption in VA | 7.5 VA 60 Hz 0.3 68 °F (20 °C) 7 VA 50 Hz 0.3 68 °F (20 °C) |
| Heat dissipation | 2...3 W 50/60 Hz |

Environment

| | |
|---------------------------------------|--------------------------|
| Ambient air temperature for operation | 23...140 °F (-5...60 °C) |
| Net Weight | 0.15 lb(US) (0.07 kg) |

Ordering and shipping details

| | |
|-----------------------|---------------------------------|
| Category | 22341 - CONTACTOR,D,K,&F ACCESS |
| Discount Schedule | I12 |
| GTIN | 00785901467892 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.15 lb(US) (0.07 kg) |
| Returnability | Yes |
| Country of origin | FR |

Packing Units

| | |
|------------------------|------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 1.57 in (4 cm) |
| Package 1 width | 1.77 in (4.5 cm) |
| Package 1 Length | 2.48 in (6.3 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |
| PVC free | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|