



Main

Range	Spacial
Product name	Spacial S3X
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	19.69 in (500 mm)
Nominal width	15.75 in (400 mm)
Nominal depth	7.87 in (200 mm)
Product installation	Wall-mounting
Device composition	1 body 1 lock door 1 door

Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Solid
Number of doors	Front face 1
Door opening side	Reversible 120 °)
Lock type	2 points lock, 3 mm double-bar
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Body and door stainless steel 304L Lock zamak Hinge stainless steel
Surface finish	Body and door Scotch-Brite® brushed Lock chromium plated
Net Weight	17.75 lb(US) (8.05 kg)

Environment

Standards	IEC 62208
Product certifications	CAN/CSA 22 UL 508 type A
IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262
Environmental characteristic	Corrosive Specific hygiene

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	00785901690160
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	BG

Packing Units

Package 1 Height	20.47 in (520.000 mm)
Package 1 width	16.14 in (410.000 mm)
Package 1 Length	8.66 in (220.000 mm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------