

# Product data sheet

## Characteristics

# 9050JCK58V20

Timing Relay, Type JCK, plug In, repeat cycle, adjustable time, 0.6 to 60 minutes, 10A, 240 VAC, 120 VAC/110 VDC



### Main

|                |                      |
|----------------|----------------------|
| Product range  | 9050JCK              |
| Product type   | Timer                |
| Timing mode    | Repeat cycle         |
| Timing range   | 0.6...60 min         |
| Supply voltage | 120 V AC<br>110 V DC |

### Complementary

|                           |                      |
|---------------------------|----------------------|
| Power consumption         | 2 VA                 |
| Current rating            | 10 A                 |
| Switch function           | DPDT                 |
| Contact composition       | 2 NO + 2 NC          |
| Contact material          | Silver nickel        |
| Maximum switching voltage | 240 V AC             |
| Mounting type             | Socket               |
| Number of pins            | 8                    |
| Shape of pins             | Tubular              |
| For use with              | 8501NR51<br>8501NR52 |

### Environment

|   |                                  |
|---|----------------------------------|
| Certifications                          | UL Listed<br>UL Recognized<br>CE |
| Ambient temperature range - operational | -18...150 °F (-28...66 °C)       |
| Height                                  | 2.40 in (61 mm)                  |
| Width                                   | 1.69 in (43 mm)                  |
| Depth                                   | 4.09 in (104 mm)                 |

### Ordering and shipping details

|                       |  |
|-----------------------|--|
| Category              | 21651 - 9050 JCK(NOT JCK60, 70) G P TIMERS |
| Discount Schedule     | CP2  |
| GTIN                  | 00785901057970                             |
| Nbr. of units in pkg. | 1  |
| Package weight(Lbs)   | 0.27 lb(US) (0.12 kg)                      |
| Returnability         | Yes  |
| Country of origin     | US   |

## Packing Units

|                  |                     |
|------------------|---------------------|
| Package 1 Height | 2.60 in (6.604 cm)  |
| Package 1 width  | 4.40 in (11.176 cm) |
| Package 1 Length | 2.00 in (5.080 cm)  |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| REACH free of SVHC         | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |
| Circularity Profile        | <a href="#">End Of Life Information</a>  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|