

HJF36150

Circuit breaker, PowerPacT H, thermal magnetic, unit mount, 150A, 3 pole, 25 kA, 600 VAC, 80% rated



Main

Range of product	PowerPacT H
Product or component type	Circuit breaker

Complementary

Line Rated Current	150 A
Number of Poles	3P
Breaking capacity code	J
Mounting mode	Unit mount
Magnetic hold current	900 A
Magnetic tripping current	1700 A
Electrical connection	Busbar connection line Busbar connection load
Tightening torque	44.25 lbf.in (5 N.m) 0.00...0.15 in ² (2.5...95 mm ²) (AWG 14...AWG 3/0)
Height	6.4 in (162.56 mm)
Width	4.12 in (104.65 mm)
Depth	4.36 in (110.74 mm)
Continuous current rating	80 %

Environment

Product certifications	CSA UL Listed CCC CE IEC
Ambient air temperature for operation	104 °F (40 °C)

Ordering and shipping details

Category	01115-HG,HJ,JG,JJ UNIT MT BREAKER/SWITCH
Discount Schedule	DE2
GTIN	00785901697534
Package weight(Lbs)	4.00 lb(US) (1.814 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	5.50 in (13.970 cm)
Package 1 width	7.50 in (19.050 cm)
Package 1 Length	8.80 in (22.352 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------