



### Main

Marketing Trade Name	QO
Product Type	Load Center Cover
Cover Type	Flush cover

### Complementary

Number of Spaces	54
Enclosure Material	Welded sheet steel
Surface Finish	Baked enamel grey
Height	40.55 in (1030 mm)
Width	15.43 in (392 mm)

### Environment

Enclosure Rating	NEMA 1 for indoor
Product Certifications	UL Listed

### Ordering and shipping details

Category	10001 - QO PON 1PH LC,12-60 CKT, MB N1
Discount Schedule	DE3A
GTIN	00785901129295
Nbr. of units in pkg.	1
Package weight(Lbs)	15.13 lb(US) (6.86 kg)
Returnability	Yes
Country of origin	US

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.30 in (3.302 cm)
Package 1 width	15.70 in (39.878 cm)
Package 1 Length	40.80 in (103.632 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	81
Package 2 Weight	1235.00 lb(US) (560.186 kg)
Package 2 Height	40.50 in (102.87 cm)
Package 2 width	40.80 in (103.632 cm)
Package 2 Length	48.00 in (121.92 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------