



Main

Product	Surface cover Door latch
Color	Gray
Cover type	Surface cover with door
Type of front plate	Ventilated

Complementary

Material	Steel
Height	92 in (2336.80 mm)
Width	20 in (508.00 mm)
Depth	5.75 in (146.05 mm)
Tightening torque	Cover 10...12 lb.in
Latch Type	3 points lock

Environment

Enclosure Rating	NEMA 1
Product certifications	CULus

Ordering and shipping details

Category	08352 - NF / NQ TRIMS RTA
Discount Schedule	PE1A
Nbr. of units in pkg.	1
Package weight(Lbs)	65 lb(US) (29.48 kg)
Returnability	No

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.