

V-Gard Accessory System

V-Gard Frames for MSA Slotted Full Brim Hats



Classification:	General purpose
Market(s):	Oil, gas & petrochemical, manufacturing, repair and maintenance, construction, general industry, forestry, shipbuilding, metalworking, automotive, mining
Application(s):	Chipping, splash, chiseling, drilling, grinding, machining, power fastening, sanding, sawing
Material:	Polybutylene terephthalate (PBT)
Color(s):	Black
Available Styles:	Frame for Slotted Full Brim Hats
Size:	Fits MSA Slotted Full Brim Hats
Features:	Offered with or without debris control
Standards¹:	ANSI/ISEA Z87.1-2010 and CSA Z94.3
Certification/Testing:	CSA International and Intertek
Min Order Qty:	10

V-GARD FRAMES FOR GENERAL PURPOSES		Part No.	Product Specifics
		10154622	• Fits MSA Slotted Full Brim Hats • Sold with replaceable debris control which creates tight seal between frame and hat • Sliding adjustment blades allow visor to work with most half-mask respirators and other PPE worn under a visor • Patented Infini-just allows lift/closure adjustment using grippable knobs that can't be lost ²
		10154604	• Fits MSA Slotted Full Brim Hats • Debris control sold separately • Sliding adjustment blades allow visor to work with most half-mask respirators and other PPE worn under a visor • Patented Infini-just allows lift/closure adjustment using grippable knobs that can't be lost ²
DEBRIS CONTROL		Part No.	Product Specifics
		10155838	• Debris Control for V-Gard Slotted Full Brim Hat Frames • Debris control exceeds EN requirements for molten metal • All-rubber construction • Min Order Qty: 10

WARNING

Use V-Gard Frames ONLY with V-Gard Visors, to ensure compliance with safety standards. Misuse can result in death, permanent impairment of sight, or other serious injury.

¹Standards requirements met by each V-Gard Frame or Headgear/V-Gard Visor combination designated on each V-Gard Visor.

²US Patent No. 9,125,448

Note: This Bulletin contains only a general description of the products shown. While uses and performance capabilities are described, under no circumstances shall the products be used by untrained or unqualified individuals and not until the product instructions including any warnings or cautions provided have been thoroughly read and understood. Only they contain the complete and detailed information concerning proper use and care of these products.

ID 0670-027-MC / Aug 2015
© MSA 2015 Printed in U.S.A.



MSA – The Safety Company
1000 Cranberry Woods Drive
Cranberry Township, PA 16066 USA
Phone 724-776-8600
www.MSAafety.com
U.S. Customer Service Center
Phone 1-800-MSA-2222
Fax 1-800-967-0398
MSA Canada
Phone 1-800-672-2222
Fax 1-800-967-0398

MSA Mexico
Phone 01 800 672 7222
Fax 52 - 44 2227 3943
MSA International
Phone 724-776-8626
Toll Free 1-800-672-7777
Fax 724-741-1553

www.MSAafety.com