



## Main

Range	TeSys
Product name	TeSys LS1
Product or component type	Fuse-disconnector
Device short name	LS1D
Poles description	3P

## Complementary

Mounting support	Rail
Mounting position	Vertical +/- 23°
Control type	Toggle
[Ue] rated operational voltage	600 V
[Ie] rated operational current	25 A power circuit
Local signalling	Blown fuse indication
Fuse size	10 x 38 mm
Fuse type	GG AM
Associated fuse rating	30 A aM 30 A gG
Connections - terminals	Spring terminals 2 0.00...0.01 in <sup>2</sup> (1...6 mm <sup>2</sup> )solid Spring terminals 2 0.00...0.01 in <sup>2</sup> (1...6 mm <sup>2</sup> )flexible without cable end Spring terminals 2 0.00...0.01 in <sup>2</sup> (1...4 mm <sup>2</sup> )flexible with cable end

## Environment

Standards	IEC 60947-2 IEC 60947-4-1 IEC 60947-1
Product certifications	UR BV
IP degree of protection	IP20
Protective treatment	TH
Ambient air temperature for operation	-58...158 °F (-50...70 °C) operation
Height	3.50 in (89 mm)
Width	1.77 in (45 mm)
Depth	2.69 in (68.3 mm)
Net Weight	0.60 lb(US) (0.27 kg)

## Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901046998
Nbr. of units in pkg.	1
Package weight(Lbs)	0.47 lb(US) (0.21 kg)

Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	0.520 dm
Package 1 width	1.100 dm
Package 1 Length	0.800 dm

### Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

### Contractual warranty

Warranty	18 months
----------	-----------