

Product data sheet

Characteristics

8538SCA24V06

NEMA Combination Starter, Type S, 30A
fusible disconnect, Size 1, 27A, 10 HP at 600
VAC polyphase, 480 VAC coil, NEMA 12



Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	10 Hp 460 V AC, 3 phase 10 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3
Disconnect Type	Fusible disconnect switch H, 30 A
NEMA size	1

Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
----------------	---

Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901744429
Nbr. of units in pkg.	1
Package weight(Lbs)	37.2 lb(US) (16.87 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	11.00 in (27.940 cm)
Package 1 width	12.80 in (32.512 cm)
Package 1 Length	29.00 in (73.660 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------