



Main

Product or component type	Motor mechanism
Range of product	Powerpact
Device application	Control
Circuit breaker type	H-frame

Complementary

[Uc] control circuit voltage	24 V DC 30 V DC
------------------------------	--------------------

Environment

Product certifications	CSA UL Listed
------------------------	------------------

Ordering and shipping details

Category	01103-H,J,COMPACT NS UL/IEC CB ACCESS
Discount Schedule	DE2
Package weight(Lbs)	16.00 oz (453.592 g)
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.