



Main

Product Type	Contactors
Product Range	Type S
Contactors Type	Reversing

Complementary

NEMA Size	2
Rated Current	45 A
Number of Poles	3P
Mounting Orientation	Horizontal
Maximum Voltage Rating	600 V AC
Phase	3 phase
Horsepower Rating	10 HP 200 V AC 15 HP 230 V AC 25 HP 460 V AC 25 HP 575 V AC
Coil Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	6.89 in (175 mm)
Width	9.02 in (229 mm)
Depth	6.02 in (153 mm)

Environment

Enclosure Type	Not rated (open device)
Certifications	CSA UL Listed

Ordering and shipping details

Category	21272 - 8702,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901724360
Nbr. of units in pkg.	1
Package weight(Lbs)	16 lb(US) (7.26 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------