



Main

Accessory / separate part designation	Incandescent bulb
Accessory / separate part type	Incandescent bulb
Accessory / separate part category	Lighting accessories
[Us] rated supply voltage	24 V AC/DC
Signalling type	Steady
Power dissipation in W	6 W
Signalling colour	Clear
Diameter	0.71 in (18 mm)
Length	1.38 in (35 mm)
Sale per indivisible quantity	1

Complementary

Bulb base	BA 15d
-----------	--------

Ordering and shipping details

Category	22611 - XVB-STACKLIGHTS
Discount Schedule	XV
GTIN	00785901764632
Nbr. of units in pkg.	10
Package weight(Lbs)	0.01 lb(US) (0.00 kg)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.89 in (4.8 cm)
Package 1 width	2.56 in (6.5 cm)
Package 1 Length	5.00 in (12.7 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	3.21 oz (91 g)
Package 2 Height	1.89 in (4.8 cm)
Package 2 width	2.56 in (6.5 cm)
Package 2 Length	5.00 in (12.7 cm)
Unit Type of Package 3	S02
Number of Units in Package 3	280
Package 3 Weight	5.76 lb(US) (2.614 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------