



Pre-Mixed Concrete Patch

Pre-mixed, water-based, for concrete repairs

©TCC Materials • March 2016 • Version 1.0

PRODUCT DESCRIPTION

SAKRETE® Pre-Mixed Concrete Patch can be used directly from the container. Smooth unsightly surface defects, minor cracks, and holes. Adheres tightly to sides of properly prepared cracks and joints to help keep out moisture, reducing pavement break-up caused by freeze-thaw action. For filling and sealing cracks up to 1 in. (25 mm) wide in concrete. May also be used for residential repairs of masonry walls and re-applying small broken pieces of concrete or tuck-pointing brick mortar joints.

WHEN/WHERE TO USE

- Vertical and horizontal patches
- Interior and exterior uses
- Concrete or masonry surfaces
- Repairs rough surfaces and holes

ADVANTAGES

- Ready to use - no mixing or dilution
- Fills and seals cracks up to 1 in. wide
- Extends the life of concrete areas
- Maintains bond and elasticity through extreme weather conditions
- Easy to apply
- 20-40 minute skim time

AVAILABLE SIZES

1 qt. (.95 L) tub (BOM 120027)

TYPICAL YIELD

1 qt. (.95 L) will cover approximately
3 sq. ft. at 1/8 in. thickness

PREPARATION

Clean all dirt, dust, and loose materials from cracks or rough surfaces with a stiff broom or stream of water. Allow to dry prior to application of Pre-Mixed Concrete Patch.

KEEP FROM FREEZING

WARNING: INJURIOUS TO EYES

KEEP OUT OF REACH OF CHILDREN

Helpful Items:



Safety Glasses



Gloves



Broom



Trowel

MIXING

No mixing is required, gently stir product before use. Do not dilute with water or solvents.

APPLICATION

Read all directions before starting work. For best results, apply in dry, warm weather. Do not apply when rain is forecasted or when the ambient air temperature is expected to fall below 50°F (10°C) within 48 hours. To fill cracks in area to be smoothed, apply Pre-Mixed Concrete Patch with cement trowel or putty knife by pressing material into crevices to improve bond. Smooth finish patch with damp application tool. For rough textured areas, trowel over surface up to 1/8 in. (3 mm) thick. Thicker applications will require longer curing and may be damaged if rain occurs before surface cures. For deeper applications, up to 1/4 in. (6 mm) thick, apply in layers of 1/8 in. (3 mm) and allow 24 hours cure time between layers.

CLEAN UP

Use warm, soapy water for cleaning hands while product is wet. Dried Pre-Mixed Concrete Patch is insoluble in water. Clean tools and spills before it dries. Hardened product remaining on tools may be removed with mineral spirits.

CURING

Product will form a skin in 20-40 minutes and harden within 4-6 hours. If painting is desired, allow Pre-Mixed Concrete Patch to cure a minimum of 48 hours (when temperatures are between 65°-75°F/18°-24°C with no rain) before painting. Use a high-quality, exterior masonry grade, breathable acrylic latex paint. Curing time will vary with thickness of application. Surface will usually cure in 48 hours but weather and thickness may slow drying. Curing to full depth of cracks may take 5-7 days. Keep traffic off the repair area during the curing period. If this cannot be done, sprinkle sand over the repair area to prevent tracking.

NOTES AND LIMITATIONS

- Rubber gloves and goggles are recommended safety equipment
- Store in tightly sealed original factory containers off the floor in a dry place
- Do not apply in cracks over 1 in. wide or on surfaces over 1/8 in. thick

Proper application and installation of all SAKRETE products are the responsibility of the end user.

WARNING

WARNING! CAUSES IRRITATION - Avoid contact with eyes, skin and clothing. Wash thoroughly after handling. Exposure may result in irritation of the skin. **FIRST AID:** In case of eye contact, flush immediately with plenty of water for at least 15 minutes and get prompt medical attention; for skin, washing thoroughly with plenty of soap and water. If irritation persists, get medical attention. **KEEP OUT OF REACH OF CHILDREN. READ and UNDERSTAND the Safety Data Sheet (SDS) before using this product.**

LIMITED PRODUCT WARRANTY

The manufacturer warrants that this product shall be free from defects in materials and workmanship, and will perform per the manufacturer product literatures in effect at the time of purchase. This warranty is for one (1) year from the date of purchase. Any implied warranty of merchantability or fitness for a particular purpose is limited to the duration of his express warranty. This warranty applies only if the product is used in strict accord with manufacturer published instruction. The sole and exclusive remedy under this warranty is replacement of the defective product or refund of the purchase price, at manufacturer's option. **CONSEQUENTIAL, SPECIAL, AND INCIDENTAL DAMAGES ARE NOT RECOVERABLE UNDER THIS WARRANTY.** All claims under this warranty must submitted to manufacturer by calling 866-725-7383. This warranty gives you specific legal rights, and you may also have other rights which vary from state to state.

SAKRETE® and the background design are registered trademarks of SAKRETE of North America LLC, Charlotte, NC 28273 • ©2006. SAKRETE® is manufactured under license from SAKRETE of North America LLC.

Shelf Life	One year in original, unopened container.
Storage Conditions	Store dry in tightly sealed original container.
Color	Gray.