

P1200S

TYPE 1 600 to 1200A SURFACE MOUNT MOULDED CASE CIRCUIT BREAKER ENCLOSURE



Main

Circuit Breaker Type	PKL PGL PLL PJL
Product Destination	Circuit breaker P 3P Circuit breaker P 2P

Complementary

Enclosure Material	Steel
Width	21.00 in (533.4 mm)
Height	52.13 in (1323.98 mm)
Depth	9.75 in (247.65 mm)
Rated Current	600...1200 A
Device Mounting	Surface
Poles Description	3P 2P

Environment

Product Certifications	UL CSA
------------------------	-----------

Environmental

NEMA Degree of Protection	NEMA 1
NEMA Degree of Protection	NEMA 1

Ordering and shipping details

Category	00030 - IND CB ENCL NEMA 1,3R
Discount Schedule	DE1
GTIN	00785901577706
Nbr. of units in pkg.	1
Package weight(Lbs)	120.81 lb(US) (54.80 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	1.11 ft (0.338 m)
Package 1 width	1.87 ft (0.569 m)
Package 1 Length	4.67 ft (1.422 m)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------