



Main

Product	Double Throw Safety Switch
Duty Rating	General duty
Disconnect Type	Non-fusible disconnect switch
Factory Installed Neutral	None
Number of Poles	3
Current Rating	600 A
Voltage Rating	240 V AC 250 V DC
Enclosure Rating	NEMA 1
Maximum Horse Power Rating	125 Hp 240 V at AC 50-60 Hz for 3 phase conforming to NEC 240.6 50 hp 250 V at DC

Complementary

Short-circuit current	10 KA H or K 200 kA R, J or T
Fuse type	H or K R, J or T
Mounting Type	Surface
Wire Size	250...500 kcmil copper or aluminium
Tightening torque	200 Lbf.In (22.60 N.m) 275 Lbf.In (31.07 N.m) 375 Lbf.In (42.37 N.m) 500 lbf.in (56.49 N.m) (250...500 kcmil)
Depth	8.88 in (225.55 mm)
Width	24.46 in (621.28 mm)
Height	63.31 in (1608.07 mm)
Net Weight	169.98 lb(US) (77.1 kg)

Environment

Certifications	UL Listed
----------------	-----------

Ordering and shipping details

Category	00160 - DE1 MISC
Discount Schedule	DE1
GTIN	00785901430063
Nbr. of units in pkg.	1
Package weight(Lbs)	180 lb(US) (81.65 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.42 ft (0.432 m)
Package 1 width	3.00 ft (0.914 m)
Package 1 Length	5.50 ft (1.676 m)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------