



Main

Product or component type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

Complementary

Line Rated Current	350 A
Number of Poles	3P
Breaking capacity code	H
Mounting Mode	I-Line
Magnetic Hold Current	1750 A
Magnetic Tripping Current	3500 A
Electrical connection	Lugs load I-Line connection line
Terminal identifier	AL400LA
Height	12.5 in (317.50 mm)
Width	6 in (152.40 mm)
Depth	4 in (101.60 mm)

Environment

Certifications	CSA UL Listed
----------------	------------------

Ordering and shipping details

Category	01040 - LA/LH BRKR, SW, MAG-GARD
Discount Schedule	DE2
GTIN	00785901339427
Nbr. of units in pkg.	1
Package weight(Lbs)	18.28 lb(US) (8.29 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	9.40 in (23.876 cm)
Package 1 width	11.50 in (29.210 cm)
Package 1 Length	17.40 in (44.196 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------