

# Product data sheet

## Characteristics

# 8903SMG2V02

Contactor, Type S, multipole lighting,  
electrically held, 30A, 3 pole, 110/120 VAC  
50/60 Hz coil, NEMA 1



### Main

Product	Electrically Held Lighting Contactor
Type	S

### Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	30 A
Number of Poles	3P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical connection	Lugs
Height	10.00 in (254 mm)
Depth	5.28 in (134 mm)
Width	5.98 in (152 mm)

### Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product certifications	UL Listed CSA

### Ordering and shipping details

Category	21325 - 8903 S (NOT S°C) ELECT.
Discount Schedule	CP1
GTIN	00785901619574
Nbr. of units in pkg.	1
Package weight(Lbs)	7.07 lb(US) (3.21 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	6.60 in (16.764 cm)
Package 1 width	6.50 in (16.510 cm)
Package 1 Length	10.70 in (27.178 cm)

## Offer Sustainability

EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------