



### Main

|                           |                 |
|---------------------------|-----------------|
| Product or component type | Circuit breaker |
|---------------------------|-----------------|

### Complementary

|                           |  |
|---------------------------|--|
| Line Rated Current        | 110 A  |
| Breaking capacity code    | B  |
| Magnetic hold current     | 1200 A   |
| Trip unit technology      | Thermal-magnetic   |
| Magnetic tripping current | 2400 A   |
| Tightening torque         | 247.82 lbf.in (28 N.m) 0.04...0.23 in <sup>2</sup> (25...150 mm <sup>2</sup> ) (AWG 4...300 kcmil) |
| Height                    | 6.47 in (164.34 mm)  |
| Width                     | 4.5 in (114.30 mm)   |
| Depth                     | 3.93 in (99.82 mm)   |
| Continuous current rating | 80 %   |


### Ordering and shipping details

|                     |                                 |
|---------------------|---------------------------------|
| Category            | 00005-QO,Q2L 2P ENCL & BREAKERS |
| Discount Schedule   | DE2A                            |
| GTIN                | 00785901702979                  |
| Package weight(Lbs) | 3.41 lb(US) (1.545 kg)          |
| Returnability       | Yes                             |
| Country of origin   | MX                              |

### Packing Units

|                  |                     |
|------------------|---------------------|
| Package 1 Height | 6.10 in (15.494 cm) |
| Package 1 width  | 6.10 in (15.494 cm) |
| Package 1 Length | 9.80 in (24.892 cm) |

### Offer Sustainability

|                           |  |
|---------------------------|--|
| Sustainable offer status  | Green Premium product  |
| California proposition 65 | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH free of SVHC        | Yes  |
| EU RoHS Directive         | Compliant  <a href="#">EU RoHS Declaration</a>  |
| Mercury free              | Yes  |

|                             |   |
|-----------------------------|---|
| RoHS exemption information  | <a href="#">Yes</a>                           |
| China RoHS Regulation       | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure    | <a href="#">Product Environmental Profile</a> |
| PVC free                    | Yes   |
| Halogen content performance | Halogen free product                          |
| <b>Contractual warranty</b> |   |
| Warranty                    | 18 months                                     |