

# Product data sheet

## Characteristics

# VLSH2S5B

Disconnect switch, TeSys VLS, protruding rotary handle, screw mounting, 65x65 mm, black handle, 5 mm shaft



### Main

Range	TeSys
Device short name	VLSH
Product or component type	Rotary handle
Range compatibility	TeSys VARIO LS VLS3P
Handle colour	Black
Handle front plate colour	Grey
Rotary handle padlocking	1 to 3 padlocks 0.16...0.31 in (4...8 mm)
Marking	0 - 1 OFF-ON

### Complementary

Fixing mode	By 4 screws
Tightening torque	20.36 lbf.in (2.3 N.m)
Base dimension	65 x 65 mm
Height	2.56 in (65 mm)
Width	2.56 in (65 mm)
Depth	2.28 in (58 mm)
Net Weight	0.15 lb(US) (0.068 kg)

### Environment

IP degree of protection	IP65
NEMA degree of protection	NEMA 1 NEMA 2 UL 508 NEMA 3R UL 508 NEMA 4 UL 508 NEMA 4X UL 508 NEMA 12 UL 508 NEMA 12K UL 508

### Ordering and shipping details

Category	21734 - TESYS VLS DISCONNECT SWITCHES
Discount Schedule	CP1
GTIN	00785901576884
Nbr. of units in pkg.	1
Package weight(Lbs)	0.16 lb(US) (0.07 kg)
Returnability	Yes
Country of origin	IT

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.36 in (6 cm)
Package 1 width	2.56 in (6.5 cm)
Package 1 Length	2.56 in (6.5 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>