

Universal Reversible USB 2.0 Hi-Speed Cable, 28/24AWG (Reversible A to 5Pin Micro B M/M) - 10 Piece Bulk Pack, 1-ft.

MODEL NUMBER: UR050-001-24-10



Description

Tripp Lite's UR050-001-24-10 1-ft. USB 2.0 A to Micro-B cable features a Universal / Reversible "A" connector, which takes the guesswork out of which way to position the "A" connector for plugging. Micro-USB is the latest generation of USB connector, and is found on Cell Phones, PDA's, Digital Cameras, Tablets and more.

Constructed of premium double-shielded cable with tinned copper braid and aluminum mylar foil featuring twisted 28AWG data lines and 24AWG power lines. 24AWG power lines allow for charging of higher powered devices such as tablets, which standard 28AWG Micro USB cables can't sufficiently charge. USB 2.0 rated cable handles 480Mbps data transfer rates. 10 Piece Bulk Pack.

Features

- USB Universal / Reversible A Male to Micro-B Male - 10 Piece Bulk Pack
- Constructed of 24AWG power lines for the charging of higher powered devices such as tablets, which standard 28AWG Micro USB cables can't sufficiently charge
- Premium double-shielded cable with tinned copper braid and aluminum mylar foil features twisted 28AWG data lines and 24AWG power lines
- Supports USB 2.0 data transfer rates up to 480Mbps

Highlights

- Universal / Reversible "A" Male to Micro-B Male - 10 Piece Bulk Pack
- Constructed of 24AWG power lines for the charging of higher powered devices such as tablets, which standard 28AWG Micro USB cables can't sufficiently charge
- Premium double-shielded cable with tinned copper braid and aluminum mylar foil features twisted 28AWG data lines and 24AWG power lines
- Supports USB 2.0 data transfer rates up to 480Mbps

System Requirements

- Digital devices that use the USB Micro-B Female socket

Package Includes

- 1-ft. USB 2.0 Universal / Reversible A to Micro-USB B Device Cable, 28/24AWG (A Male to Micro-B Male) - 10 Piece Bulk Pack

Specifications

SELECTOR	
Selector Type	CABLES
General Info	
Product Group	USB & FIREWIRE CABLES



TAA Compliant	No
OVERVIEW	
Intended Application	Connecting Peripherals
Style	USB
Cable Types	USB
Cable Type	USB
INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.3
Cable Length Ranges	1 - 2
UPC ASSIGNMENT	
Unit Carton UPC#	037332186157
PHYSICAL	
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)
CONNECTIONS	
Connector A	REVERSIBLE USB A (MALE)
Connector B	MICRO-USB B (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.