



Main

Range	I-Line
-------	--------

Complementary

Main Type	Universal Mains
Width	26.16 in (664.46 mm)
Height	65.4 in (1661.16 mm)
Product Destination	Panelboard interior HCP-SU 26 in (660.40 mm) 86 in (2184.40 mm)
Rated Current	800 A
Mounting Space	54 in (1371.60 mm)

Ordering and shipping details

Category	00016 - I-LINE PB RTA
Discount Schedule	PE1A
GTIN	00785901002581
Nbr. of units in pkg.	1
Package weight(Lbs)	180 lb(US) (81.65 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	0.78 ft (0.239 m)
Package 1 width	3.18 ft (0.968 m)
Package 1 Length	5.76 ft (1.755 m)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------
