



Main

Range	I-Line
Product or Component Type	Drip hood

Complementary

Width	8.943 in (227.15 mm)
Height	32 in (812.80 mm)
Depth	2.52 in (64.01 mm)
Product Destination	Panelboard HCM 32 in (812.80 mm) 48 in (1219.20 mm) 8.25 in (209.55 mm)
Device Mounting	Surface

Environment

Standards	CULus CE
-----------	-------------

Ordering and shipping details

Category	00016 - I-LINE PB RTA
Discount Schedule	PE1A
GTIN	00785901416920
Nbr. of units in pkg.	1
Package weight(Lbs)	9.74 lb(US) (4.42 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	6.20 in (15.748 cm)
Package 1 width	14.00 in (35.560 cm)
Package 1 Length	32.50 in (82.550 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------
