



### Main

Range of product	ConneXium
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Product or component type	Shielded twisted pair straight cable
Accessory / separate part destination	Ethernet network
Cable length	6.56 ft (2 m)

### Complementary

Transmission support medium	Twisted shielded pairs cable
Communication network category	5e
AWG gauge	AWG 24
Electrical connection	2 connectors, RJ45 straight 8
Marking	UL
Cover material	PVC

### Environment

IP degree of protection	IP20
Standards	EN 50173 class D EIA/TIA-568 category CAT 5E IEC 11801 class D CMG FT4 UL 444

### Ordering and shipping details

Category	18225 - PLC NTRK HRDWR & PROWORX SOFTWARE
Discount Schedule	PC41
GTIN	00785901174356
Nbr. of units in pkg.	1
Package weight(Lbs)	0.27 lb(US) (0.12 kg)
Returnability	No
Country of origin	TH

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.39 in (1 cm)
Package 1 width	7.87 in (20 cm)
Package 1 Length	8.66 in (22 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------