

D325NTR

Safety switch, general duty, fusible, 400A, 3 poles, 50 hp, 240 VAC, NEMA 3R, neutral factory installed



Main

Product	Single Throw Safety Switch
Duty Rating	General duty
Device application	Residential
Disconnect Type	Fusible disconnect switch
Factory Installed Neutral	Neutral (factory installed)
Phase	3 phase
Number of Poles	3
Current Rating	400 A
Voltage Rating	240 V AC
Enclosure Rating NEMA	NEMA 3R
Maximum Horse Power Rating	50 hp 240 V at AC 60 Hz for 3 phase conforming to NEC 240.6

Complementary

Short Circuit Current Rating	100 kA T
Fuse type	T
Mounting Type	Surface
Electrical Connection	Lugs
Wiring configuration	4-wire (3PH + G)
Wire Size	AWG 10...AWG 6 aluminium/copper
Tightening torque	340 lbf.in (38.41 N.m) (AWG 1/0...250 kcmil)
Depth	10.13 in (257.30 mm)
Width	22.25 in (565.15 mm)
Height	30.63 in (778.00 mm)
Net Weight	61.73 lb(US) (28 kg)

Environment

Certifications	UL listed file E2875
----------------	----------------------

Ordering and shipping details

Category	00059 - MISC G/D SWITCHES
Discount Schedule	DE1A
GTIN	00785901003656
Nbr. of units in pkg.	1
Package weight(Lbs)	70.7 lb(US) (32.07 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	10.80 in (27.432 cm)
Package 1 width	23.00 in (58.42 cm)
Package 1 Length	31.50 in (80.01 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

