



Main

Range of product	Harmony 9001K
Product or component type	Pilot light
Device short name	K

Complementary

Bezel material	Chromium plated metal
Mounting diameter	1.18 in (30 mm)
Lens type	Domed glass
Cap/operator or lens colour	Red
Light source	incandescent
Bulb base	BA 9s
Light block supply	Via transformer 120 V AC 50/60 Hz Via integral transformer 110 V AC 50/60 Hz
Connections - terminals	Screw clamp terminals, 1 x 0.22...2 x 1.5 mm ² IEC 60947-1
Shape of screw head	Round
Operating position	Any position
[Us] rated supply voltage	110...120 V AC
Operating mode	Normal
Device presentation	Complete product

Environment

Product certifications	CSA LR25490 class 3211 03 CE UL listed file E42259 CCN NKCR
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901860112
Nbr. of units in pkg.	50
Package weight(Lbs)	0.49 lb(US) (0.22 kg)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.80 in (4.572 cm)
Package 1 width	2.10 in (5.334 cm)
Package 1 Length	3.60 in (9.144 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------