

PC 667



SPECIALTY GRADE, OUTDOOR STUCCO DUCT TAPE



TYPICAL APPLICATIONS

- For protective masking of non-painted surfaces, including steel, vinyl, aluminum and anodized metals
- Use in plastering, stucco, concrete, pool and tile applications

PRODUCT FEATURES

- 14-day UV-resistant
- Easy to tear
- Removes cleanly
- Made using Polybonded CO-EX Technology®

CONSTRUCTION

Overall Grade/Function: Specialty/Extended outdoor
Backing: Waterproof, UV-resistant polyethylene film
with a cloth carrier
Adhesive: Blended rubber

STANDARD WIDTH(S)

1.88. in

STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

STANDARD CORE SIZE

3 in

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



RED
(RED)



WHITE
(WHI)

PHYSICAL PROPERTIES	STANDARD	METRIC
---------------------	----------	--------

Tensile Strength	26 lbs/in width	45.5 N/10 mm
Adhesion to Stainless Steel	50 oz/in width	5.47 N/10 mm
Thickness	9 mils	0.23 mm
Elongation	23%	23%
Service Temperature Range	50 F to 200 F	10 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PTSC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent product specifications or a guarantee of product performance. Individual rolls may vary from these standards (or physical properties). The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

