

# Product data sheet

## Characteristics

# 2510KR1H

Switch, manual, 20A, 2 pole, 3 HP at 575 VAC, single phase, toggle operated, no indicator, NEMA 7&9, two conduit opening



### Main

|         |                           |
|---------|---------------------------|
| Product | Single Unit Manual Switch |
| Type    | K                         |

### Complementary

|                        |  |
|------------------------|--|
| Current Rating         | 20 A   |
| Cable Entry            | 0.75 NPT (top and bottom)  |
| Horsepower Rating      | 2 Hp 115 V AC<br>2 Hp 230 V AC<br>3 Hp 460 V AC<br>3 Hp 575 V AC<br>1 Hp 90 V DC<br>2 Hp 115 V DC<br>1.5 hp 230 V DC |
| Maximum Voltage Rating | 600 V AC<br>230 V DC   |
| Number of Poles        | 2P   |
| Control Unit Type      | Toggle   |
| Number of Phases       | 1 phase  |
| Pilot Light            | No indicator   |
| Starter Type           | Non reversing  |
| Electrical Connection  | Screw clamp terminals  |
| Wire Gauge             | AWG 14...AWG 10 copper   |
| Height                 | 6.36 in (161.54 mm)  |
| Width                  | 3.95 in (100.33 mm)  |
| Depth                  | 4.35 in (110.49 mm)  |

### Environment

|                       |   |
|-----------------------|---|
| Certifications        | UL listed file E58760 CCN NPXZ<br>CSA LR26817 class 3218 04 |
| NEMA Enclosure Rating | NEMA 3R/7/9 Cast Aluminium standard size                    |

### Ordering and shipping details

|                       |                          |
|-----------------------|--------------------------|
| Category              | 21102 - 2510,2511,2512 K |
| Discount Schedule     | CP1                      |
| GTIN                  | 00785901376392           |
| Nbr. of units in pkg. | 1                        |
| Package weight(Lbs)   | 3.6 lb(US) (1.63 kg)     |
| Returnability         | Yes                      |
| Country of origin     | MX                       |

## Packing Units

|                  |                     |
|------------------|---------------------|
| Package 1 Height | 5.50 in (13.970 cm) |
| Package 1 width  | 4.70 in (11.938 cm) |
| Package 1 Length | 7.00 in (17.780 cm) |

## Offer Sustainability

|                           |   |
|---------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH free of SVHC        | Yes   |
| EU RoHS Directive         | Not compliant   |
| China RoHS Regulation     | <a href="#">China RoHS Declaration</a>  |
| PVC free                  | Yes   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|