

IRT220 Non-Contact 12:1 Laser IR Thermometer

Instantly measure the temperature of objects without making contact

Features:

- Built-in laser identifies the measurement area
- Backlit LCD display with selectable °F or °C readout
- 0.95 fixed emissivity
- Min/Max to monitor lowest and highest measurement readings
- Automatic Data Hold
- Auto power off after 10 seconds
- Complete with 9V battery
- Optional model complete with Certificate of Traceability to N.I.S.T.
- 1-year warranty

Applications:

- Measure the surface temperature of objects that are too hot to touch or hard to reach
- Measure moving objects



NIST
TRACEABLE
CALIBRATION
AVAILABLE

Specifications

Temperature Range	-4 to 932°F (-20 to 500°C)
Accuracy	±2%
Resolution	0.1°F/°C
Distance to Target Ratio	12:1
Response Time	500ms
Emissivity	0.95 fixed
Power	9V battery
Dimensions	5.4 x 2.9 x 1.5" (137 x 73 x 39mm)
Weight	5.2oz (148.5g)



Ordering Information:

IRT220 Non-Contact 12:1 Laser IR Thermometer
IRT220-NIST IRT220 Including Certificate of Traceability to N.I.S.T.

CE