

# RHT02 & RHT05 Hygro-Thermometer Pens

Two models provide humidity/temperature measurements, with option of wetbulb & dew point

## Features:

- °F/°C switchable
- Data Hold freezes the reading on the display
- Min/Max records the highest and lowest readings
- Auto power off with disable
- Built-in Humidity calibration mode
- Includes CR2032 battery
- Optional models complete with Certificate of Traceability to N.I.S.T.
- 1-year warranty

## Model RHT05:

- Dual display simultaneously displays Humidity and Air Temperature, or Wet Bulb, or Dew Point

## Applications:

- Building inspection, water restoration, greenhouses, warehouses, museums, libraries, offices, storage areas



## Specifications

	RHT02	RHT05
Air Temperature	-4 to 140°F (-20 to 60°C)	-4 to 140°F (-20 to 60°C)
Accuracy	±1.1°F/0.6°C	±1.1°F/0.6°C
Relative Humidity	0 to 100%RH	0 to 100%RH
Accuracy	±3%RH (10 to 90%RH)	±3%RH (10 to 90%RH)
Wet Bulb	—	-4 to 139.8°F (-20 to 59.9°C)
Dew Point	—	23 to 140°F (-5 to 59.9°C)
Resolution	0.1°F/°C; 0.1%RH	0.1°F/°C; 0.1%RH
Power	1 CR2032 Battery	1 CR2032 Battery
Dimensions	6.9 x 1.7 x 0.6"	6.9 x 1.7 x 0.6"
Weight	(175 x 42 x 16mm)	(175 x 42 x 16mm)

## Ordering Information:

- RHT02 Hygro-Thermometer Pen  
 RHT02-NIST RHT02 with certificate of NIST traceability  
 RHT05 Hygro-Thermometer Pen with Dew Point and Wetbulb  
 RHT05-NIST RHT05 with certificate of NIST traceability

