

# AM

## MEDIUM TEMP MEDIUM GRADE PAPER MASKING TAPE

## INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

### DESCRIPTION

AM is an aqua colored, conformable, saturated, crepe paper masking tape with pressure-sensitive rubber adhesive. Good adhesion and holding properties. Clean, easy removal. Resists paint flaking and wet sanding. Compatible with both water and solvent-based paints. Three (3) day UV resistance. Temperature resistant up to 225°F (107°C) for 30 minutes.

### PRODUCT APPLICATION

For paint masking requiring adhesion to and removal from a variety of surfaces.

### NOMINAL VALUES

The following data are nominal values based on PSTC, ASTM and other standard tests. The data should not be considered as specifications.

<b>Backing</b>	Crepe Paper
<b>Adhesive</b>	Natural Rubber / Resin
<b>Tensile Strength</b> (lbs/in. width) ASTM D3759	20 (87.5 N/25mm)
<b>Elongation</b> (% at break) ASTM D3759	12
<b>Adhesion to Steel</b> (oz./in. width) ASTM D3330	28 (7.6 N/25 mm)
<b>Quick Stick</b> (oz/in. width) PSTC-5	
To kraft	5 (1.4 N/25mm)
To steel	14 (3.8 N/25mm)
<b>Total Thickness</b> (mils) ASTM D-3652	6.6 (0.17 mm)
<b>Color</b>	Aqua (Blue-Green)



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA  
Customer Service: 800.IPG.8273 | 800.474.8273  
Tape Technical Service: 877.447.4832  
www.itape.com | info@itape.com



While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 10/19

