


Specifications



Aerator 1.2 gpm (4.5 L/min)

Model: 180158

DESCRIPTION

- Body Acetal
- Int. o-ring EPDM
- Ext. o-ring Silicone
- Continuous temperature 120 degrees F Max
- Continuous pressure 90 psi Max
- Includes aerator key

FLOW

• Pressure compensating for constant flow from 20 to 80 psi

WARRANTY

 Warranted for 5 years against material or manufacturing defects when used in commercial applications

www.moen.com

3/16