MOEN[®]

There is more than 1 version of this model. Page down to identify the version you have.

PRODUCT DESCRIPTION

- Battery powered, sensor activated, exposed water urinal flushometer with brass angle stop valve
- · Brass construction with chrome plated finish
- · Chloramine resistant seals
- 3/4" IPS inlet supply
- 3/4" top spud
- · High back pressure vacuum breaker
- All flush valves are intended for use with compatible flush volume fixtures as specified by the fixture manufacturer. WaterSense® labeled flush valves should be used with a WaterSense® labeled fixture that has a compatible flush volume to ensure complete system performance.

OPERATION

- Self-cleaning Accuset[™] piston flush technology
- Mechanical override
- · Adjustable infrared sensor range up to 15"
- · Four (4) Alkaline AA batteries included
- · Battery life: Up to 8 years*
- · Low battery indicator light
- Optional 24 hour Sentinel Flush (factory setting is off)
- · Operating Pressure Range: 20-125psi

FLOW RATE

□8312 (1.0gpf/3.8Lpf)

 \square 8315 (0.5gpf/1.9Lpf) - WaterSense® certified

□8316 (0.125 gpf/0.5Lpf) - WaterSense® certified

STOP VALVE


- All metal 3/4" IPS vandal resistant angle stop with double o-ring connection
- · Adjustable installation (left or right connection)

STANDARDS

- Third party certified to meet: ASSE1037 / ASME A112.1037 / CSA125.37, ASME A112.19.2 / CSA B45.1 and all applicable requirements referenced therein
- BAA
- ADA 🖶

WARRANTY

- · Warranted for 5 years against material or manufacturing defects
- * Typical alkaline battery life at 130 uses per day is about 8 years



CRITICAL DIMENSIONS

(DO NOT SCALE)

Specifications




M•POWER™ 3/4" Battery Powered Sensor Exposed Style Urinal Flush Valve

Models: 8312, 8315, 8316







MOEN[®]

PRODUCT DESCRIPTION

- Brass construction w/chrome plated finish
- 3/4" IPS supply
- 3/4" top spud
- All flush valves are intended for use with compatible flush volume fixtures as specified by the fixture manufacturer. WaterSense® labeled flush valves should be used with a WaterSense® labeled fixture that has a compatible flush volume to ensure complete system performance.

OPERATION

- Adjustable sensor eye
- Battery powered (4) standard AA (included)
- Average battery life 250,000 cycles
- Self-diagnostic electronics
- Piston flushing mechanism
- Self cleaning filter system
- Low battery indicator light

□8312(1.0gpf/3.8Lpf)

□8315 (0.5gpf/1.9Lpf) - WaterSense® certified

□8316 (0.125 gpf/0.5Lpf) - WaterSense® certified

- Operating pressures 10 to 125 psi
- 24 hour sentinel flush
- Mechanical manual override button

STOP VALVE

- 3/4" IPS angle stop (vandal resistant)
- Adjustable installation (left or right connection)


Third party certified to meet: ASSE1037 / ASME A112.1037 / CSA125.37, ASME A112.19.2 / CSA B45.1 and all applicable requirements referenced therein

ADA 🕒

WARRANTY

Warranted for 5 years against material or manufacture defects.


Specifications



3/4" Battery Powered Sensor **Exposed Style Urinal Flush Valve**

Models: 8312, 8315, 8316





(DO NOT SCALE)

FOR MORE INFORMATION CALL: 1-800-BUY-MOEN

www.moen.com

Rev. 2/20