

Garant**Pipe thread cutting set in a plastic case, for parallel pipe threads: G1/8-1****Order data**

Order number	145905 G1/8-1
GTIN	4045197878564
Item class	11K

Description**Version:**

Sturdy plastic case with carrying handle and 2 catches. Each tool is securely stored and protected in a foam insert and is immediately ready to hand. For more detailed descriptions of the content see individual products.

Application:

For **Whitworth parallel pipe threads** DIN ISO 228/1

Content:

- 1 set each hand tap No. 130550: Size 5.5
- 1 each die No. 142050: Size 1/8; 1/4; 3/8; 1/2; 3/4; 1
- 1 each adjustable tap wrench No. 148410: Size 3; 5
- 1 each die stock No. 149310: Size 30×11; 38×10; 45×14; 55×16; 65×18
- 1 screwdriver No. 664122: Size 5.5

Technical description

for parallel pipe threads	G1/8 - G1
Thread type	G

Flank angle	55 degrees
Type of product	Die

Accessories

Tap wrench, adjustable Type 5	148410 5
Screwdriver for slot-head, short, with 2-component Haptoprene handle Blade width b 5,5 mm	664122 5,5
Die G G3/8	142050 G3/8
Hand tap set G G1/8	130550 G1/8
Die stock for die Ø × height 30X11 mm	149310 30X11
Die G G3/4	142050 G3/4
Die G G1/4	142050 G1/4
Hand tap set G G1/2	130550 G1/2
Die G G1/2	142050 G1/2
Hand tap set G G1/4	130550 G1/4
Die stock for die Ø × height 55X16 mm	149310 55X16
Hand tap set G G3/4	130550 G3/4
Tap wrench, adjustable Type 3	148410 3
Die G G1	142050 G1
Die stock for die Ø × height 45X14 mm	149310 45X14
Hand tap set G G3/8	130550 G3/8
Die G G1/8	142050 G1/8
Hand tap set G G1	130550 G1
Die stock for die Ø × height 38X10 mm	149310 38X10
Die stock for die Ø × height 65X18 mm	149310 65X18