

**HOLEX****Mini LED floodlight, Type: 7****Order data**

Order number	081573 7
GTIN	4062406242473
Item class	02A

**Description****Version:**

Compact and powerful cordless LED floodlights for mobile use. The compact dimensions mean they are perfectly suitable for use as hand lamps. The adjustable magnetic bases allow them to be used as stationary light sources.

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

Supplied with USB-C charging cable.

**Technical description**

ATEX zone	no
Type of rechargeable battery	Lithium-ion
Bulb	LED module
Overall length	89 mm

Weight	255 g
IP Index of Protection	IP 65
Illumination step 2	350 lm
Illumination	100 lm
Power supply	Rechargeable battery-powered
Illumination time stage 2	4 h
Battery capacity	2.6 Ah
Overall width	30 mm
Overall height	95 mm
Illumination time	10 h
Battery voltage	3.7 V
Number of rechargeable batteries contained	1
Illumination step 3	700 lm
Illumination time stage 3	2 h
Type of product	Floodlight