

Garant**Die Left-hand thread, M-LH: M2,5****Order data**

Order number	140620 M2,5
GTIN	4045197083616
Item class	11K

Description**Version:**

Closed, pre-slit form.

1 3/4 turns lead chamfer.

Cutting direction: left-hand

Tolerance class: DIN 13 6g

Pitch: 0.45 mm

External Ø: 16 mm

Height: 5 mm

Technical description

Pitch	0.45 mm
Height	5 mm
External Ø	16 mm
Tolerance class	DIN 13 6g
Thread size	M2.5

Thread type	M-LH
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Cutting direction	left-hand
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		