

Garant**High-precision countersink set, long No. 150377 in a case 90°, TiAlN, Number of countersinks: 6****Order data**

Order number	150375 6
GTIN	4045197912220
Item class	11M

Description**Version:**

Handy for assembly and workshop use.

High-precision countersink No. 150377, **with long shank.**

Application:

High-precision countersinks for chatter-free production of **precise, round 90° countersunk surfaces.**

Content:

1 pc. each countersink: Size 6.3; 8.3; 10.4; 12.4; 16.5; 20.5

Supplied with:

6-piece countersink set in a case.

Technical description

Number of cutting edges Z	3
Number of countersinks	6
Coating	TiAlN

Countersink tip angle	90 degrees
Tool material	HSS
Spacing of the countersink cutting edges	unequal spacing
Standard	Manufacturer's standard
Shank	Parallel shank to h9
Colour ring	green
Type of product	Stepped drill and countersink

Accessories

High-precision countersink, long90° External Ø Dc 16,5 mm	150377 16,5
High-precision countersink, long90° External Ø Dc 6,3 mm	150377 6,3
High-precision countersink, long90° External Ø Dc 8,3 mm	150377 8,3
High-precision countersink, long90° External Ø Dc 10,4 mm	150377 10,4
High-precision countersink, long90° External Ø Dc 20,5 mm	150377 20,5
High-precision countersink, long90° External Ø Dc 12,4 mm	150377 12,4