



Countersink set No. 150175 in a case 90°, uncoated, Number of countersinks: 17



Order data

Order number	150320 17
GTIN	4045197086068
Item class	12M

Description

Version:

Countersink sets **in a case**. Handy for assembly and workshop use.

All countersinks have 3 cutting edges, radially relieved.

Flutes are ground from solid.

High precision countersinks for chatter-free countersinking.

Content:

1× each countersink: Size 4.3; 5; 6; 6.3; 7; 8; 8.3; 10; 10.4; 11.5; 12.4; 15; 16.5; 19; 20.5; 23; 25

Note:

Empty case for 6 or 7 countersinks, see No. 150370.

Technical description

Number of countersinks	17
Number of cutting edges Z	3
Coating	uncoated
Countersink tip angle	90 degrees

Tool material	HSS
Standard	DIN 335 C
Shank	Plain shank with h9
Colour ring	without
Type of product	Stepped drill and countersink

Accessories

Countersink90° External Ø Dc 11,5 mm	150175 11,5
Countersink90° External Ø Dc 15 mm	150175 15
Countersink90° External Ø Dc 7 mm	150175 7
Countersink90° External Ø Dc 8 mm	150175 8
HOLEX Pro Steel high-precision countersink with unequal spacing90° External Ø Dc 4,3 mm	150182 4,3
HOLEX Pro Steel high-precision countersink with unequal spacing and 3 drive flats90° External Ø Dc 4,3 mm	150184 4,3
Countersink90° External Ø Dc 12,4 mm	150175 12,4
Countersink90° External Ø Dc 4,3 mm	150175 4,3
Countersink90° External Ø Dc 16,5 mm	150175 16,5
Countersink90° External Ø Dc 6 mm	150175 6
Countersink90° External Ø Dc 10,4 mm	150175 10,4
Countersink90° External Ø Dc 19 mm	150175 19
Countersink90° External Ø Dc 5 mm	150175 5
Countersink90° External Ø Dc 10 mm	150175 10
Countersink90° External Ø Dc 25 mm	150175 25
Countersink90° External Ø Dc 8,3 mm	150175 8,3
Countersink90° External Ø Dc 20,5 mm	150175 20,5
Countersink90° External Ø Dc 23 mm	150175 23
Countersink90° External Ø Dc 6,3 mm	150175 6,3