



Tap wrench, adjustable, Type: 4



Order data

Order number	148410 4
GTIN	4062406210410
Item class	12L

Description

Version:

With hardened jaws and steel grips. For use in confined spaces one steel handle can be unscrewed.

For **standard** use: Zinc die-cast body.

Technical description

Overall length	480 mm
for hand reamer Ø DIN 206	7 - 20 mm
Capacity <input type="checkbox"/>	5.5 - 16 mm
for hand taps DIN 352	M9 – M27
Standard	DIN 1814
Type of product	Tap wrench