

**Sheet metal drill HSS single-sided, uncoated, Ø DC h8: 6,4mm****Order data**

Order number	113341 6,4
GTIN	4045197964571
Item class	12B

Description**Version:**

Extremely break-resistant due to short helix and strong core taper. Self-centring point.

Cylindrically ground on circumference(without chamfers) to prevent jamming.

Vaporised surface.

Dimensions similar to DIN 1897.

Point geometry shape C.

Application:

Especially for drilling sheet metal.

Technical description

Tolerance nominal Ø	h8
Flute length L _c	21 mm
Standard	DIN 1897
Overall length L	70 mm
Number of cutting edges Z	2
recommended maximum drilling depth L ₂	11.4 mm
Nominal Ø D _c	6.4 mm
Point angle	135 degrees
Coating	uncoated
Tool material	HSS
Through-coolant	no

Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable only under restricted conditions		
dry	suitable		