

Garant
Die Hexagon, M: M14

Order data

| | |
|--------------|---------------|
| Order number | 140920 M14 |
| GTIN | 4045197083913 |
| Item class | 11K |

Description
Version:

External hexagon for standard socket size. **Without** tapered spiral point. **1¾ turns lead chamfer.**

Note:

For re-cutting damaged threads or for cutting where access is difficult.

Tolerance class: DIN 13 6g

Pitch: 2 mm

Width across flats: 36 mm

Height: 14 mm

Technical description

| | |
|--------------------|-------|
| Width across flats | 36 mm |
| Height | 14 mm |
| Pitch | 2 mm |
| Thread size | M14 |
| Thread type | M |

| | |
|-----------------|-----------|
| Flank angle | 60° |
| Tool material | HSS |
| Standard | DIN 382 |
| Tolerance class | DIN 13 6g |
| Type of product | Die |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | | |
| Steel < 500 N/mm ² | suitable | | |
| Steel < 750 N/mm ² | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1100 N/mm ² | suitable only under restricted conditions | | |
| INOX < 900 N/mm ² | suitable only under restricted conditions | | |
| CuZn | suitable only under restricted conditions | | |
| Oil | suitable | | |
| dry | suitable only under restricted conditions | | |