

**Garant****LED cordless work light, Type: 200****Order data**

Order number	081441 200
GTIN	4062406232900
Item class	01A

**Description****Version:**

Versatile LED cordless work lamp in slim sturdy design with a wide range of applications. Practical monitoring of the state of charge of the battery by LED display directly on the lamp.

- **Main lamp steplessly dimmable from 10 - 100 %.**
- **Integral spotlight function.**
- **Flexible use thanks to 180° pivoting magnetic base, together with fold-up and rotating suspension hook.**

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

Supplied with USB-C charging cable and plug-in power supply unit.

**Note:**

For mounting on Easyfix perforated panels, order the Easyfix plastic base plate No. 955820 size 2 also.

**Technical description**

Overall length	200 mm
Number of rechargeable batteries contained	1
Weight	157 g
Illumination	20 - 200 lm
Power supply	Rechargeable battery-powered
IP Index of Protection	IP 65
Battery voltage	3.7 V
ATEX zone	no
Overall width	39 mm
Battery capacity	1.2 Ah
Illumination time	2 - 20 h
Bulb	LED module
Type of rechargeable battery	Lithium-ion
Type of product	Work lamp

## Accessories

USB charger Type CABLE	081432 CABLE
Cordless lamp spare parts Type 1	081434 1
Li-ion battery Battery capacity 1200 mAh	081431 1200
USB charger Type CHARGER	081432 CHARGER