

Garant
Die Hexagon, M: M16

Order data

Order number	140920 M16
GTIN	4045197083920
Item class	11K

Description
Version:

External hexagon for standard socket size. **Without** tapered spiral point. **1¾ turns lead chamfer.**

Note:

For re-cutting damaged threads or for cutting where access is difficult.

Tolerance class: DIN 13 6g

Pitch: 2 mm

Width across flats: 41 mm

Height: 18 mm

Technical description

Width across flats	41 mm
Height	18 mm
Pitch	2 mm
Thread size	M16
Thread type	M

Flank angle	60°
Tool material	HSS
Standard	DIN 382
Tolerance class	DIN 13 6g
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1100 N/mm ²	suitable only under restricted conditions		
INOX < 900 N/mm ²	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
Oil	suitable		
dry	suitable only under restricted conditions		