

**LED pocket rechargeable work light, Type: 118****Order data**

Order number	081576 118
GTIN	4062406262037
Item class	02A

Description**Version:**

Handy powerful rechargeable pocket LED work light. Steplessly dimmable main beam and additional spotlight function. Attachment by means of a strong magnet or fold-away suspension hook.

Function:

IP30: Protected against penetration by foreign bodies with $\varnothing > 2.5$ mm, however tools and wires should be kept away, and offers no protection against water.

Supplied with:

Including USB charging cable.

Technical description

Type of rechargeable battery	Lithium-ion
Illumination	50 - 500 lm
Weight	114 g
ATEX zone	no

Battery capacity	3.7 Ah
IP Index of Protection	IP 30
Illumination time	1 - 10 h
Battery voltage	1.5 V
Overall width	47 mm
Power supply	Rechargeable battery-powered
Overall length	108 mm
Number of rechargeable batteries contained	1
Bulb	LED module
Type of product	Work lamp