

Jobber drill set HSS No. 114020 in a case, uncoated, Type: 1-10



Order data

Order number	115030 1-10
GTIN	4045197024169
Item class	12B

Description

Version:

Composed of jobber drills DIN 338.

Roll forged, standard helix angle, core thickness, and core taper.

Robust jobber drill with strengthened core and small chisel point for easy spot drilling and accurate centring of the designated hole. **Precision roll forged flutes.**

Technical description

Incremental steps of drills	0.5 mm
Drill range	1 - 10 mm
Number of drills	19
Shank	Plain shank
Number of cutting edges Z	2
Coating	uncoated
Tool material	HSS
Standard	DIN 338

Type	N
Tolerance nominal Ø	h8
Point angle	118 degrees
Through-coolant	no
with case	yes
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	45 m/min	N
Steel < 500 N/mm ²	suitable	40 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
GG(G)	suitable only under restricted conditions	25 m/min	K
Uni	suitable only under restricted conditions		
Oil	suitable		
wet maximum	suitable		

Accessories

HSS jobber drill Precision roll forged N Ø DC h8 4 mm	114020 4
HSS jobber drill Precision roll forged N Ø DC h8 6,5 mm	114020 6,5
HSS jobber drill Precision roll forged N Ø DC h8 8 mm	114020 8
HSS jobber drill Precision roll forged N Ø DC h8 7,5 mm	114020 7,5
HSS jobber drill Precision roll forged N Ø DC h8 10 mm	114020 10
HSS jobber drill Precision roll forged N Ø DC h8 9 mm	114020 9

HSS jobber drill Precision roll forged N Ø DC h8 2,5 mm	114020 2,5
HSS jobber drill Precision roll forged N Ø DC h8 3,5 mm	114020 3,5
HSS jobber drill Precision roll forged N Ø DC h8 1 mm	114020 1
HSS jobber drill Precision roll forged N Ø DC h8 5 mm	114020 5
HSS jobber drill Precision roll forged N Ø DC h8 1,5 mm	114020 1,5
HSS jobber drill Precision roll forged N Ø DC h8 6 mm	114020 6
HSS jobber drill Precision roll forged N Ø DC h8 8,5 mm	114020 8,5
HSS jobber drill Precision roll forged N Ø DC h8 2 mm	114020 2
HSS jobber drill Precision roll forged N Ø DC h8 5,5 mm	114020 5,5
HSS jobber drill Precision roll forged N Ø DC h8 9,5 mm	114020 9,5
HSS jobber drill Precision roll forged N Ø DC h8 3 mm	114020 3
HSS jobber drill Precision roll forged N Ø DC h8 4,5 mm	114020 4,5
HSS jobber drill Precision roll forged N Ø DC h8 7 mm	114020 7
Empty case for jobber drills to DIN 338 Type 1-10	115475 1-10