

Garant**Collet chuck, extra slim, HSK-A 63 A = 160, Clamping range: 2-6mm****Order data**

Order number	304974 2-6
GTIN	4045197708397
Item class	31A

Description**Version:**

- **HSK mating faces machined.**
- **Shanks hard turned.**
- **With RFID/Balluffchip bore.**
- **The collet is clamped by a threaded connection from behind through the chuck, no clamping nut required.**

Advantage:

Extremely slim design permits machining of components where access is difficult, e.g. during toolmaking and mould-making.

Application:

For clamping tools with plain shank to DIN 6499.

Supplied with:

Clamping screw and wrench with T-handle.

Optional extras:

Plug-in socket No. 309890, **GARANT collets No. 309563.**

Technical description

Clamping range	2 - 6 mm
Ø D ₁	9.6 mm
Ø D ₂	13 mm
Overhang dimension A	160 mm

External Ø D	27 mm
Adapter	HSK-A 63 A = 160
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 5 µm
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Collet chuck