

**Garant**
**Clamping toolholder STGCR 90°, for indexable inserts TC., right-hand,  
Shank / insert size: 20/16mm**

**Order data**

Order number	260906 20/16
GTIN	4045197713261
Item class	21T

**Technical description**

Functional width $L_4$	25 mm
Head length $L_1$	22 mm
Shank size	20 mm
Shim screw	269013 2
Pack of insert screws	269028 2
Shim	269005 7
Insert size	16 mm
ISO code toolholder	STGCR/L 2020K16
suitable indexable insert	TC.. 16T3..
Overall length L	125 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle $\kappa$	90 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 7	269005 7
Set of insert screws Type 18	269028 18
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15